

# 24-Port 0.5U Rack-Mount Cat6/Cat5 110 Patch Panel 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N252-024-HU



### Highlights

- 24 port Cat6 Patch Panel in a Half-U Panel
- 19-in. rackmount ready
- 110 type punch-down termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- 0.5U Cat6 24-port Patch Panel
- 24 Nylon wire ties
- 4 Mounting screws
- Installation Guide

### Description

The N252-024-HU Cat6 patch panel frees up valuable rack space by condensing 24 RJ45 ports into a Half-U panel. This unique panel features a built-in strain relief bar, allowing cables to be wire-tied (24 ties included) to the bar, taking stress off the 110 punch-down connector. The panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Cat6 connecting hardware specifications. Color coded for both EIA/TIA 568A and 568B installations. 24 ports ensure a wide range of plug-and-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs.

### Features

- Unique 0.5U Height
- Category 6 Gigabit Rated
- UL approved
- Ports clearly numbered both on front and back
- Built-in strain relief bar
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame EIA/TIA 2/32 spacing
- Rack mountable on a 19 rack (0.5U of space)
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332160560
Product Type	Rackmount
Technology	Cat5/5e; Cat6



Powering Business Worldwide



CONNECTIONS	
Number of Ports	24
Side A - Connector 1	110 IDC
Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	1.50 x 3.80 x 19.80
Shipping Dimensions (hwd / cm)	3.81 x 9.65 x 50.29
Shipping Weight (lbs.)	1.50
Shipping Weight (kg)	0.68
Panel Style	Punchdown
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.