

Cat5e/Cat6 24-Port Patch Panel - Shielded, Krone IDC, 568B, RJ45 Ethernet, 1U, TAA

MODEL NUMBER: N252-024-SH-K



Shielded 24-port patch panel organizes mission-critical Cat5e/Cat6 cable connections in your high-speed Ethernet network.

Features

Shielded 24-Port Patch Panel Organizes and Manages High-Speed Cat6 Network Cabling Manage your high-density Cat5e/6 application without taking up too much valuable rack space. The N252-024-SH-K offers 24 fully shielded RJ45 ports with color-coded Krone IDC slots that are terminated using a proper punch-down tool. The patch panel supports T568B wiring standards and is fully rated for 5 Gbps data transfer speeds in your Ethernet application. Both the rear and front connectors are numbered and labeled for custom naming to help you identify individual cable runs at a glance.

Mounts in 1U of Space in Your 19 in. Enclosure or Open Frame Rack The UL-approved patch panel supports mounting in 1U of space in your EIA-standard 19-inch rack enclosure or open frame rack. It comes with grounding wire, cable ties and a strain relief bar to help cut down on cord clutter, organize your connections, take stress off the Krone connectors and maintain stable performance.

TAA-Compliant for GSA Schedule Purchases The N252-024-SH-K is compliant with the Federal Trade Agreements Act (TAA). It is eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

Highlights

- Rated for 5 Gbps speeds for managing high-speed cabling in mission-critical Ethernet applications
- 24 RJ45 ports numbered, labeled and color-coded for easy cable identification
- 1U patch panel easy to mount for immediate use in your EIA-standard 19 in. rack
- Supports EIA/TIA T568B wiring standards for Krone-type terminations
- Complies with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Applications

- Connect security cameras, sensors, routers, computers, switches, wireless access points and other network devices in a high-speed Ethernet setup

Package Includes

- N252-024-SH-K Cat6 24-Port Patch Panel, 1U
- (6) Cable ties
- (4) Screws
- Grounding wire
- Installation guide

Specifications

OVERVIEW	
UPC Code	037332236166
Technology	Cat5/5e; Cat6



PHYSICAL	
Color	Black
Rack Height	1U
Shipping Dimensions (hwd / cm)	5.59 x 10.41 x 51.82
Shipping Dimensions (hwd / in.)	2.20 x 4.10 x 20.40
Shipping Weight (kg)	1.22
Shipping Weight (lbs.)	2.70
COMMUNICATIONS	
Network Speed Details	Rated for 5GbE
CONNECTIONS	
Ports	24
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	KRONE IDC
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>