

## 48-Port 1U Rack-Mount Cat6/Cat5 High Density 110 Patch Panel, 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N252-048-1U



### Highlights

- Space saving CAT6 Rated 48-port 1U 110 type Patch panel
- Removable "upper-deck" for easy punch down termination
- Built-in wire management loom
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- 48port, 1U, Cat6 110 punch down patch panel

### Description

Tripp Lite's 1U, 48port, Cat6 High Density Patch panel frees up valuable rack real estate by condensing a typical 2U 48 port patch panel into 1U of space. The unique design allows for easy punch down termination. Simply unscrew 4 slotted thumbscrews to remove the "upper deck" punch down array. Punch down the "lower deck" cables first, then replace the upper deck, and punch down upper array. Integrated wire loom keeps cabling tidy and easy to route. Heavy Duty 14GA cold rolled steel construction. 110 connectors are color coded for either 568A or 568B wiring.

UTP Cat6 22-24 AWG solid cable

### Features

- Space saving CAT6 Rated 48-port 1U 110 type Patch panel
- Removable "upper-deck" for easy punch down termination
- Built-in wire management loom
- Color coded for 568A/568B wiring
- Heavy Duty 14ga cold rolled steel construction
- Mounts in standard 19" Racks or Cabinets

## Specifications

OVERVIEW	
UPC Code	037332151735
Technology	Cat5/5e; Cat6
PHYSICAL	
Color	Black



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Dimensions (hwd / cm)	5.08 x 49.53 x 9.40
Shipping Dimensions (hwd / in.)	2.00 x 19.50 x 3.70
Shipping Weight (kg)	1.80
Shipping Weight (lbs.)	3.96
Unit Dimensions (hwd / cm)	4.45 x 48.26 x 10.16
Unit Dimensions (hwd / in.)	1.75" x 19" x 4"
Unit Weight (kg)	1.63
Unit Weight (lbs.)	3.60
<b>CONNECTIONS</b>	
Ports	48
Side A - Connector 1	110 IDC
Side B - Connector 1	RJ45 (FEMALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>