



10GBase CX4 Cable, 5M (16-ft.)

MODEL NUMBER: N263-05M



Highlights

- 5 Meter CX4 Cable
- Works with any manufacturers' 10Gb XenPak
- Made with Premium Madison TurboTwin™ cable
- Compliant with the IEEE Draft specification P802.3ak/D5.3

System Requirements

 Ethernet switches with CX4 / Xenpak modules for 10Gbps linking

Package Includes

10 GBase CX4 Cable (5 Meter)

Description

Tripp Lite's high-speed 10Gbps CX4 Cables provide an ultra high-performance, cost-effective solution for Gigabit Copper applications. Featuring 28AWG Madison TurboTwin™ twinaxial cable, these cables utilize up to 3.125 gigabytes per second wire speed connections with four channels. Cables work with any manufacturers' 10Gbps Xenpak transceivers that utilize the Ejector style latch connector. Tripp Lite CX4 cables are available in 0.5 meter, 1 meter, 3 meter, and 5 Meter lengths.

Features

- 5 Meter CX4 Cable
- Flexible 28AWG Madison TurboTwin™ Cable
- Ejector style latch mechanism
- Connects the CX4 modules between two switches
- Fully 802.3ak compliant
- RoHS Compliant

Specifications

OVERVIEW	
UPC Code	037332149916
CONNECTIONS	
Side A - Connector 1	CX4 [SFF-8470] (MALE)
Side B - Connector 1	CX4 [SFF-8470] (MALE)
Angled Connector	No
PHYSICAL	
Cable Jacket Color	Black





Cable Length (ft.)	16.4	
Cable Length (m)	5.00	
Cable Length (in.)	196.8	
Shipping Dimensions (hwd / in.)	0.50 x 6.20 x 8.90	
Shipping Dimensions (hwd / cm)	1.27 x 15.75 x 22.61	
Shipping Weight (lbs.)	0.90	
Shipping Weight (kg)	0.41	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
IP68 Rated	No	
Snagless Connector	No	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.