

Cisco-Compatible SFP-25G-SR-S SFP28 Transceiver - 25GBase-SR, Multimode LC, 850 nm, 328.08 ft. (100 m)

MODEL NUMBER: N286-25G-SR-S



Links a multimode Gigabit Ethernet network cable to a Cisco switch or server's SFP28 port.

Features

SFP28 Transceiver Designed for Connection to Your Cisco Network Switch or ServerThis SFP28 transceiver allows you to connect a multimode fiber optic cable to a 25 Gbps network router, server or switch. It transmits data up to 328.08-ft. (100 m) using an 850 nm wavelength. The zinc housing protects against electromagnetic interference (EMI) and excessive power dissipation.

Functionally Equivalent to Cisco SFP-25G-SR-S Transceiver ModuleThe MSA-compliant N286-25G-SR-S functions just like the equivalent Cisco SFP-25G-SR-S transceiver module and is manufactured to meet or exceed Cisco specifications. You can use this transceiver with any compatible Cisco router, server or switch and receive the same performance as the SFP-25G-SR-S.

Hot-Swappable for Installation Without Network InterruptionThis input/output device is fully hot-swappable, so you can install it without a potentially costly 25 Gbps network shutdown or device reboot. Just plug the SFP28 end of the transceiver into your Cisco network device. The other end has an LC duplex connector to link with multimode fiber optic cable (sold separately). A push/pull tab connector is easily accessible in high-density data center applications and makes the plug-and-play transceiver easy to install and remove with one hand.

Specifications

OVERVIEW	
UPC Code	037332248466
Brand Compatibility	Cisco
PHYSICAL	
Unit Dimensions (hwd / in.)	0.330 x 0.530 x 2.230

Highlights

- SFP28 transceiver module 100% compatible with Cisco's equivalent module
- Provides 25 Gbps throughput up to 328.08-ft. (100 m) via multimode fiber cabling
- LC duplex female connector supports 25GBase-SR signal at 850 nm wavelength
- Hot-swappable interface lets you install and uninstall without shutting down
- Meets or exceeds MSA standards and works in all MSA-compliant platforms

Applications

- Install an additional LC duplex port on a Cisco router, server or switch for the purpose of connecting a multimode Gigabit Ethernet network cable

System Requirements

- Cisco or other compatible network router, server or switch

Package Includes

- N286-25G-SR-S Cisco-Compatible SFP-25G-SR-S SFP28 Transceiver

Unit Dimensions (hwd / cm)	0.85 x 1.34 x 5.66
Unit Dimensions (hwd / mm)	8.5 x 13.4 x 56.6
ENVIRONMENTAL	
Operating Temperature Range	32° to 158°F (0° to 70°C)
Storage Temperature Range	-40° to 185°F (-40° to 85°C)
Relative Humidity	5% to 85%
Operating Temperature	32 to 158 F (0 to 70 C)
COMMUNICATIONS	
Network Compatibility	25 Gbps
Wavelength	850nm
Transmission Distance	100 m
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (FEMALE)
Side B - Connector 1	SFP28 (Male)
FEATURES & SPECIFICATIONS	
Data Transfer Rate	25 Gbps
Multi-Source Agreement (MSA) Compliant	Yes
Optical Port	LC
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty