

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/SC), 4M (13.12 ft.)

MODEL NUMBER: N316-04M



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/LC connectors

Package Includes

- 4 Meter Duplex MMF Cable LC/SC 62.5/125 Fiber

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 4-meter connectors: 2 SC/LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated

Specifications

OVERVIEW	
UPC Code	037332133083
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2
Technology	Multimode
Optical Mode	OM1
INPUT	
Cable Length (ft.)	13.1
Cable Length (m)	4



Cable Length (in.)	157.5
PHYSICAL	
Color	Orange
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.50
Shipping Weight (kg)	0.03
Shipping Weight (lbs.)	0.06
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	SC DUPLEX (MALE)
SPECIAL FEATURES	
Push/Pull Tabs	No
STANDARDS & COMPLIANCE	
Certifications	ROHS
Approvals	FDDI and OFNR rated
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>