

## Duplex Multimode 62.5/125 Fiber Patch Cable (LC/SC), 76M (250 ft.)

MODEL NUMBER: N316-76M



### Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/LC connectors

### Package Includes

- 76 meter ( 250ft ) Duplex MMF Cable LC/SC 62.5/125 Fiber

### Description

Tripp Lite's 76-meter ( 250ft ) multimode duplex fiber optic SC/LC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has LC to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 76-meter (250ft) Connectors: 2 SC/LC connectors on each end
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)

## Specifications

OVERVIEW	
UPC Code	037332135001
Technology	Multimode
Optical Mode	OM1
PHYSICAL	
Color	Orange
Clad Diameter	125 micron



Core Diameter	62.5 micron
Number of Fibers	2
Cable Length (ft.)	249.3
Cable Length (m)	76
Cable Length (in.)	2992.1
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 5.08
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 2.00
Shipping Weight (kg)	0.37
Shipping Weight (lbs.)	0.81
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
<b>COMMUNICATIONS</b>	
Network Speed	1Gbps
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side A - Connector 2	SC DUPLEX (MALE)
Side B - Connector 1	SC DUPLEX (MALE)
<b>SPECIAL FEATURES</b>	
Push/Pull Tabs	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	ROHS
Approvals	FDDI and OFNR rated
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>