

Duplex Multimode 62.5/125 Fiber Patch Cable (LC/LC) - Red, 5M (16 ft.)

MODEL NUMBER: N320-05M-RD



Highlights

- Manufactured from 62.5/125 duplex (Zipcord) fiber with Red jacket
- Length: 5 meter Connectors: LC connector on each end
- Insertion loss testing performed on every connector (0.2dB typical)

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC connectors

Package Includes

- 5M Duplex MMF Cable LC/LC 62.5/125 Micron Fiber Red Jacket

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- Red PVC jacket
- Length: 5 meter Connectors: LC connector on each end
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) and OFNR rated

Specifications

| OVERVIEW | |
|-------------------------|--------------|
| UPC Code | 037332130792 |
| Technology | Multimode |
| Optical Mode | OM1 |
| PHYSICAL | |
| Cable Jacket Color | Red |
| Connector Color | Gray |
| Cable Jacket Material | LSZH |
| Cable Jacket Rating | OFNR |
| Clad Diameter (microns) | 125 |
| Core Diameter (microns) | 62.5 |
| Number of Fibers | 2 |

| | |
|--------------------------------------|---------------------------------|
| Cable Length (ft.) | 16.4 |
| Cable Length (m) | 5.00 |
| Cable Length (in.) | 196.9 |
| Minimum Bend Radius | 20 mm (Dynamic); 10 mm (Static) |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50 |
| Shipping Dimensions (hwd / cm) | 22.86 x 17.78 x 1.27 |
| Shipping Weight (lbs.) | 0.07 |
| Shipping Weight (kg) | 0.03 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 to 140 F (-20 to 60 C) |
| Storage Temperature Range | -4 to 140 F (-20 to 60 C) |
| Operating Humidity Range | 5% to 85% RH, Non-Condensing |
| Storage Humidity Range | 35% to 65% RH, Non-Condensing |
| COMMUNICATIONS | |
| Network Compatibility | 1 Gbps (Gigabit); 10 Gbps |
| Attenuation @ 850NM | 3.0 dB/km |
| Insertion Loss | 0.20 dB |
| CONNECTIONS | |
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side B - Connector 1 | LC DUPLEX (MALE) |
| Endface Polish | PC |
| FEATURES & SPECIFICATIONS | |
| Push/Pull Tabs | No |
| Breakout | No |
| Trunk | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.