


Duplex Singlemode 9/125 Fiber Patch Cable (LC/SC), 25M (82 ft.)

MODEL NUMBER: N366-25M



Features

- Manufactured from 9/125 duplex (zipcord) fiber
- PVC jacket
- Length: 25 meters (82ft). Connectors: 2 x SC; 2 x LC
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Fiber made from glass (not a polymer)
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

| OVERVIEW | |
|--------------------|--------------|
| UPC Code | 037332125996 |
| Technology | Singlemode |
| Optical Mode | OS2 |
| PHYSICAL | |
| Cable Jacket Color | Yellow |
| Clad Diameter | 125 micron |
| Core Diameter | 9 micron |
| Number of Fibers | 2 |

Highlights

- Premium PVC 9/125 micron singlemode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Twice the bandwidth throughput of multimode cable

System Requirements

- Any fiber optic hardware or NIC card requiring singlemode duplex cable with LC/SC connectors

Package Includes

- 25-meter (82ft) Duplex Singlemode Fiber Patch Cable, LC/SC



| | |
|-------------------------------------|-----------------------------|
| Cable Length (ft.) | 82 |
| Cable Length (m) | 25 |
| Cable Length (in.) | 984.3 |
| Shipping Dimensions (hwd / cm) | 25.40 x 17.78 x 2.54 |
| Shipping Dimensions (hwd / in.) | 10.00 x 7.00 x 1.00 |
| Shipping Weight (kg) | 0.15 |
| Shipping Weight (lbs.) | 0.32 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 to 140 °F (-20 to 60 °C) |
| Storage Temperature Range | -4 to 140 °F (-20 to 60 °C) |
| CONNECTIONS | |
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side B - Connector 1 | SC DUPLEX (MALE) |
| SPECIAL FEATURES | |
| Push/Pull Tabs | No |
| STANDARDS & COMPLIANCE | |
| Approvals | FDDI and OFNR rated |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>