


Singlemode can support 40GBASE-PLR4 / 100GBASE-PSM4 in applicable parallel optics networks

## MTP/MPO (APC) to 4xLC (UPC) Singlemode Breakout Patch Cable, 40/100 GbE, QSFP+ 40GBASE-PLR4, Plenum, Yellow, 3 m (10 ft.)

MODEL NUMBER: N390-03M-8LC-AP



Premium 9/125 singlemode fiber optic cabling for transmitting 40/100 Gb data and voice signals. Designed for high-density fiber patching between data center MDFs and IDF's in enterprise installations.

### Features

#### 9/125 Rated Singlemode Cable for 40/100 Gb Ethernet Applications

- Designed for high-density fiber patching between data center MDFs and IDF's in enterprise installations
- Optimized for QSFP+ 40GBASE-PLR4 and QSFP28 100GBASE-PSM4 networks
- Plenum-rated jacket suited for ceilings, walls and ducts
- Yellow-colored for identification as a singlemode cable

#### MTP/MPO APC and LC Duplex UPC Connectors with Push/Pull Tabs

- MTP/MPO female connector and 8 LC duplex male connectors—no splicing required
- 12-fiber MTP/MPO connector 12 times denser than SC connector
- APC connector angled to prevent light from reflecting back into laser
- UPC connector with premium-grade ceramic ferrule for 10 GbE and faster applications
- Push/pull tabs easy to install and remove with one hand

#### Error-Free Signal Transfer

- Fully transmits 40GBASE-PLR4 with 4 fibers transmitting at 10 Gbps in each direction
- 100% tested for low insertion loss and back reflection
- Slim, space-saving uniboot design easier to manage in crowded applications

## Specifications

### Highlights

- Push/pull tab connectors install/remove with one hand
- 12-fiber MTP/MPO connectors with 12x density of SC connectors
- Slim space-saving uniboot design for easy cable management
- Angled APC connectors protect laser against destabilization
- Yellow color for quick singlemode identification

### Package Includes

- N390-03M-8LC-AP MTP/MPO to 8xLC Singlemode Breakout Patch Cable, Yellow, 3 m

<b>OVERVIEW</b>	
UPC Code	037332205599
Technology	Singlemode
Optical Mode	OS2
<b>PHYSICAL</b>	
Cable Jacket Color	Yellow
Connector Color	Blue; Green; Black
Cable Jacket Material	PVC
Cable Jacket Rating	OFNP
Clad Diameter (microns)	125
Core Diameter (microns)	9
Number of Fibers	8
Cable Length (ft.)	9.8
Cable Length (m)	2.99
Cable Length (in.)	118.1
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.17
Shipping Weight (kg)	0.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 to 140 F (-20 to 60 C)
Storage Temperature Range	-4 to 140 F (-20 to 60 C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	40 Gbps; 100 Gbps; 400 Gbps
Attenuation @ 1310NM	0.36 dB/km
Attenuation @ 1550NM	0.22 dB/km
Insertion Loss	MPO 0.70 dB; LC 0.30 dB
<b>CONNECTIONS</b>	
Side A - Connector 1	12-STRAND MTP/MPO (FEMALE)

Side B - Connector 1	(8) LC DUPLEX (MALE)
Endface Polish	APC; UPC
<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	Yes
Breakout	Yes
Trunk	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty