


## MTP/MPO (APC) Singlemode Slim Trunk Cable, 24-Strand, 40/100 GbE, 40/100GBASE-PLR4, Plenum, 6mm Dual Jacket, 15 m (49 ft.)

MODEL NUMBER: N392-15M-3X8-AP



### Highlights

- Push/pull tab connectors easily install/remove with one hand
- Factory-terminated 8-fiber MTP/MPO connectors
- Angled APC connectors protect laser against destabilization
- 100% tested for low insertion loss and back reflection
- Yellow color for easy singlemode identification

### Package Includes

- N392-15M-3X8-AP MTP/MPO Singlemode Slim Trunk Cable, Yellow, 15 m

Premium 8.3/125 singlemode fiber optic cabling for transmitting 40/100 Gb data and voice signals. Designed for high-density connections between network equipment in telecom rooms and data centers.

### Features

#### 8.3/125 Rated Singlemode Cable for 40/100 Gb Ethernet Applications

- Designed to extend high-density connections between network equipment in telecom rooms and data centers
- Recommended for patching between data center MDFs and IDFs
- Optimized for QSFP+ 40GBASE-PLR4 and QSFP28 100GBASE-PSM4 networks
- 6 mm dual plenum-rated jacket and bend-insensitive fiber perfect for ceilings, walls and ducts
- Yellow-colored for identification as a singlemode cable

#### Factory-Terminated MTP/MPO APC Connectors with Push/Pull Tabs

- 8-fiber female connectors 12 times denser than SC connectors
- Push/pull tab connectors easy to install and remove with one hand
- Angled connectors prevent light from reflecting back into laser
- 100% tested for low insertion loss and back reflection

## Specifications

OVERVIEW	
UPC Code	037332205452
Technology	MTP/MPO; Singlemode



<b>PHYSICAL</b>	
Color	Yellow
Clad Diameter	125 micron
Core Diameter	8.3 micron
Number of Fibers	8
Cable Length (ft.)	49.2
Cable Length (m)	15
Cable Length (in.)	590.6
Shipping Dimensions (hwd / cm)	11.99 x 26.01 x 26.01
Shipping Dimensions (hwd / in.)	4.72 x 10.24 x 10.24
Shipping Weight (kg)	1.10
Shipping Weight (lbs.)	2.43
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 TO 140 F (-20 TO 60 C)
Storage Temperature Range	-4 TO 140 F (-20 TO 60 C)
<b>COMMUNICATIONS</b>	
Network Speed	10Gbps / 40Gbps / 100Gbps
<b>CONNECTIONS</b>	
Side A - Connector 1	(3) 8-STRAND MTP (FEMALE)
Side A - Connector 2	(3) 8-STRAND MTP (FEMALE)
Side B - Connector 1	(3) 8-STRAND MTP (FEMALE)
<b>SPECIAL FEATURES</b>	
Push/Pull Tabs	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>