

## Fiber Optic Mode Conditioning Patch Cable (ST/LC), 3M (9.84 ft.)

MODEL NUMBER: N422-03M



### Highlights

- 3 Meter LC/ST Mode Conditioning Cable
- 62.5/125 and 8.3/125
- Run 1000Base-LX Gigabit Ethernet over MMF by offsetting signal loss
- IEEE 802.3z Gigabit Ethernet Compliant

### Package Includes

- 3 Meter LC/ST Mode Conditioning Cable

### Features

- Use Singlemode Transceivers on Multimode Fiber Backbones
- 62.5/125 and 8.3/125
- Offsets the Singlemode Laser launch from the center of a Multimode fiber
- Available in a variety of connector combinations

## Specifications

OVERVIEW	
UPC Code	037332129918
Clad Diameter	125 micron; 125 micorn
Core Diameter	62.5 micron; 8.3 micron
Number of Fibers	2
Technology	Mode Conditioning
INPUT	
Cable Length (ft.)	9.8
Cable Length (m)	3
Cable Length (in.)	118.1
PHYSICAL	
Color	Orange; Yellow



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.12
<b>CONNECTIONS</b>	
Side A - Connector 1	LC DUPLEX (MALE)
Side B - Connector 1	ST DUPLEX (MALE)
<b>SPECIAL FEATURES</b>	
Push/Pull Tabs	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>