

High-Density Fiber Cassette Sleeve, 0U, 1-Cassette Capacity

MODEL NUMBER: N482-00U



Highlights

- Holds a single Tripp Lite N482-Series cassette
- Mounts to metal surface via attached magnets
- Made from heavy-duty cold-rolled steel
- No added heat or cooling load
- Ideal for connecting 10, 40 and 100/120 GbE equipment

Package Includes

- High-Density Fiber Cassette Sleeve, 0U, 1-Cassette Capacity

Mounts a single fiber cassette to a rack without the extra expense of a 1U chassis or to an area without an existing rack infrastructure, including remote workstations, new build-outs and temporary applications.

Description

The N482-00U High-Density Fiber Cassette Sleeve is a cost-effective solution for adding a single N482-Series fiber cassette to your network application without buying a chassis. Made of heavy-duty cold-rolled steel, this space-saving 0U sleeve mounts to the metal surface of your EIA-standard 19-inch rack or cable manager via two attached magnets.

The N482-00U is recommended for adding an extra cassette to a rack application without the expense of a new 1U chassis, as well as adding fiber connectivity where no existing rack infrastructure exists, such as a remote workstation, new build-out or temporary install location. It reduces cable clutter by allowing you to connect cables at the cable manager through which they are being routed.

The N482-00U accommodates Tripp Lite N482-Series cassettes, including LC and MTP/MPO connector types. It allows you to connect 10 GbE, 40 GbE and 100/120 GbE network equipment with elegance, ease and little cost. The fully passive sleeve adds no heat or cooling load.

Features

Cost-Effective, Space-Saving Solution for Adding a Fiber Cassette to Your System

- Holds a single Tripp Lite N482-Series fiber cassette
- Attaches to metal rack enclosures and cable managers with included magnets
- Expands an installation without purchasing a new 1U chassis
- Adds network connectivity to areas without existing infrastructure
- Ideal for connecting 10 GbE, 40 GbE and 100/120 GbE network equipment
- Connects cables at cable manager through which they're being routed



- Fully passive with no added heat or cooling load
- Made from heavy-duty cold-rolled steel

Specifications

OVERVIEW	
UPC Code	037332202451
Technology	MTP/MPO; Multimode
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	5.08 x 11.68 x 26.42
Shipping Dimensions (hwd / in.)	2.00 x 4.60 x 10.40
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Unit Dimensions (hwd / in.)	3.5 x 1.3 x 8.7
ENVIRONMENTAL	
Operating Temperature Range	-4 to 122 F (-20 to 50 C)
STANDARDS & COMPLIANCE	
Approvals	RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>