


Guaranteed compatibility when used with recommended Tripp Lite cabling. Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845- Series cables.

40 GB Pass-Through Cassette, (x12) 12-Fiber MTP/MPO (Female)

MODEL NUMBER: **N482-12M12-X2**



Installs in select Tripp Lite fiber enclosure panels to create up to twelve 40 GB 12-fiber MTP/MPO connections in high-density network applications.

Description

The N482-12M12-X2 40 GB Pass-Through Cassette works in tandem with Tripp Lite's N482-01U or N482-02U Fiber Enclosure Panels to create up to twelve 12-fiber MTP/MPO connections in high-density network applications.

The cassette's modular design installs easily in the N482-01U and N482-02U enclosure panels with no tools required. Just insert the cassette into the panel, and push in its retention clips to secure it. Plug 40 GB 12-fiber MTP/MPO patch cables into the cassette to connect up to 12 network feeds. Up to five N482-12M12-X2 cassettes fit in the N482-01U 1U enclosure panel for a total of 60 network feeds, and up to 14 cassettes fit in the N482-02U 2U panel for a total of 168 network feeds. Guaranteed compatibility when used with recommended Tripp Lite cabling. Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845- Series cables.

With a heavy-duty steel housing and factory-terminated connectors that reduce time and labor, the N482-12M12-X2 is made from only the finest materials to ensure fast installations and optimal performance.

Features

Elegant, Simple Solution for 40 GB 12-Fiber MTP/MPO Connections

- High-density fiber cassette for use with Tripp Lite N482-01U and N482-02U fiber enclosure panels
- Connect up to twelve 40 GB 12-fiber MTP/MPO cables
- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845- Series cables

Highlights

- For use with Tripp Lite N482-01U or N482-02U enclosure panels
- Connect up to twelve 40 GB 12-fiber MTP/MPO cables
- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845- Series cables
- Simple installation with no tools required
- Factory-terminated connectors
- Heavy-duty steel housing

System Requirements

- Guaranteed compatibility when used with recommended Tripp Lite cabling
- Designed specifically for use with Tripp Lite cables, such as the N842-, N844- and N845- Series cables

Package Includes

- 40 GB Pass-Through Cassette, (x12) 12-Fiber MTP/MPO
- Quick Start Guide



Simple Fiber Installations Save Time and Money

- Push/pull retention clips for easy installation with no tools required
- Install up to 5 in N482-01U 1U enclosure panel for up to 60 network feeds total
- Install up to 14 in N482-02U 2U enclosure panel for up to 168 network feeds total

Premium Construction for Optimal Performance

- Heavy-duty steel construction
- Factory-terminated connectors reduce time and labor

Specifications

OVERVIEW	
UPC Code	037332191359
Technology	Multimode; MTP/MPO
PHYSICAL	
Shipping Dimensions (hwd / cm)	6.10 x 9.91 x 6.10
Shipping Dimensions (hwd / in.)	2.40 x 3.90 x 2.40
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
CONNECTIONS	
Ports	12
Side A - Connector 1	12-STRAND MTP (FEMALE)
Side B - Connector 1	12-STRAND MTP (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>