

Important Note

Guaranteed compatibility when used with recommended cabling. Designed specifically for use with N846-Series cables.

100Gb/120Gb Pass-Through Cassette - (x6) 24-Fiber MTP/MPO (Female)

MODEL NUMBER: **N482-6M24-6M24**



Description

The N482-6M24-6M24 is a high-density 100/120 Gb Pass-Through Cassette with (x6) 24-Fiber MTP/MPO connections. For use with N482-01U and N482-02U high-density Fiber Enclosure Panels. Up to five cassettes per N482-01U or up to 14 cassettes per N482-02U. Guaranteed compatibility when used with recommended cabling. Designed specifically for use with N846-Series cables. Installation is simple, with the cassette being easily installed or removed using push/pull tabs to lock or unlock it from the panel; no tools required. Furthermore, each cassette features factory-terminated connectors that reduce the time and labor required of field connector terminations. Constructed of heavy-duty steel housing.

Features

- High Density Fiber Cassette for use with N482-01U and N482-02U High Density Fiber Enclosure Panels
- 100/120Gb Pass-through Cassette, with (x6) 24-Fiber MTP/MPO connections
- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with cables, such as the N846-Series cables
- Installation is simple, with the cassette being easily installed or removed using push / pull tabs to lock or unlock it from the panel; no tools required.
- Factory terminated connectors reduce the time and labor required of field connector terminations
- Constructed of heavy-duty steel housing

Highlights

- High Density Fiber Cassette for use with N482-01U and N482-02U High Density Fiber Enclosure Panels
- 100/120Gb Breakout Cassette, with (x6) 24-Fiber MTP/MPO connections (Female)
- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with cables, such as the N846-Series cables
- Factory terminated connectors reduce the time and labor required of field connector terminations

System Requirements

- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with N846-Series cables

Package Includes

- N482-6M24-6M24 100/120Gb Breakout Cassette - (x6) 24-Fiber MTP/MPO
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332184566
Technology	Multimode



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Number of Ports	6
Side A - Connector 1	24F MTP/MPO (FEMALE)
Side B - Connector 1	24F MTP/MPO (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.10 x 2.40
Shipping Dimensions (hwd / cm)	6.10 x 10.41 x 6.10
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	1.200 x 3.500 x 0.900
Unit Dimensions (hwd / cm)	3.05 x 8.89 x 2.29
Unit Weight (lbs.)	0.18
Unit Weight (kg)	0.08
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.