

16-Port Fiber Patch Panel, 1U (SC/SC), Multimode or Singlemode

MODEL NUMBER: N490-016-SCSC



Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125, 50/125, and Singlemode 8.3/125
- 16 ports in 1U of rackspace

Package Includes

- 16 Port SC/SC Duplex Multimode / Singlemode Fiber Optic Patch Panel

Description

Tripp Lite's 16-Port 1U Rackmount SC/SC Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-thru duplex multimode connectors are mounted on a 16-gauge, cold rolled, black powder coated steel panel. Use with 62.5/125 or 50/125 multimode fiber patch cables, as well as 8.3/125 Singlemode. Panel measures 19" wide by 1.75" high.

Features

- 16 ports SC/SC
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 Multimode fiber patch cables, and 8.3/125 Singlemode
- Available in ST/ST, SC/SC, LC/LC,

Specifications

OVERVIEW	
UPC Code	037332135322
Technology	Multimode
PHYSICAL	
Shipping Dimensions (hwd / cm)	10.16 x 7.62 x 55.12
Shipping Dimensions (hwd / in.)	4.00 x 3.00 x 21.70
Shipping Weight (kg)	0.59



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	1.30
CONNECTIONS	
Ports	16
Side A - Connector 1	SC DUPLEX (FEMALE)
Side B - Connector 1	SC DUPLEX (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>