

Duplex Multimode 62.5/125 LSZH Fiber Optic Cable, 1000 ft. Bulk

MODEL NUMBER: N549-01K



Highlights

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen (LSZH) jacket
- Zip-Cord Style

Package Includes

Carton of 1,000ft Duplex 62.5/125 Multimode cable

Description

Tripp Lite N549-01K bulk 62.5/125 multimode fiber optic cable is ideal for long backbone runs, or for making your own Fiber patch cables. Individual fibers surrounded by Kevlar yarn for maximum tensile strength and protection. Low-Smoke, Zero Halogen (LSZH) jacket.

Features

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen jacket
- Zip-Cord Style
- Cable marked every meter
- Temp Range: -20C to +70C
- Suitable for Indoor Use
- 7lb Reel

Specifications

OVERVIEW	
UPC Code	037332142924
Clad Diameter	125 micron
Core Diameter	62.5 micron
Number of Fibers	2
Optical Mode	OM1



INPUT	
Cable Length (ft.)	1000
Cable Length (m)	304.8
Cable Length (in.)	12000
PHYSICAL	
Color	Orange
Shipping Dimensions (hwd / cm)	26.01 x 26.01 x 11.94
Shipping Dimensions (hwd / in.)	10.24 x 10.24 x 4.70
Shipping Weight (kg)	2.72
Shipping Weight (lbs.)	6.00
ENVIRONMENTAL	
Operating Temperature Range	-20C to +70C
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Side A - Connector 1	62.5 BULK
Side B - Connector 1	62.5 BULK
FEATURES & SPECIFICATIONS	
Technology	Multimode
SPECIAL FEATURES	
Push/Pull Tabs	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>