

Duplex Multimode 62.5/125 LSZH Fiber Optic Cable, 1000 ft. Bulk

MODEL NUMBER: N549-01K



Highlights

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen (LSZH) jacket
- Zip-Cord Style

Package Includes

Carton of 1,000ft Duplex 62.5/125 Multimode cable

Features

- Bulk 62.5/125 Multimode Duplex Fiber Optic Cable
- Low-Smoke, Zero Halogen jacket
- Zip-Cord Style
- Cable marked every meter
- Temp Range: -20C to +70C
- Suitable for Indoor Use
- 7lb Reel

Specifications

OVERVIEW	
UPC Code	037332142924
Technology	Multimode
Optical Mode	OM1
PHYSICAL	
Cable Jacket Color	Orange
Connector Color	Orange
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Clad Diameter (microns)	125

Core Diameter (microns)	62.5
Number of Fibers	2
Cable Length (ft.)	1000
Cable Length (m)	304.88
Cable Length (in.)	12000
Minimum Bend Radius	20MM (Dynamic); 10MM (Static)
Shipping Dimensions (hwd / in.)	10.24 x 10.24 x 4.70
Shipping Dimensions (hwd / cm)	26.01 x 26.01 x 11.94
Shipping Weight (lbs.)	6.00
Shipping Weight (kg)	2.72
ENVIRONMENTAL	
Operating Temperature Range	-4 to 140 °F (-20 to 60 °C)
Storage Temperature Range	-4 to 140 °F (-20 to 60 °C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
COMMUNICATIONS	
Attenuation @ 850NM	3.0dB/Km
CONNECTIONS	
Side A - Connector 1	62.5 BULK
Side B - Connector 1	62.5 BULK
FEATURES & SPECIFICATIONS	
Push/Pull Tabs	No
Breakout	No
Trunk	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2022 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.