

#### Important Note

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks.

## 10Gb Duplex Multimode 50/125 OM3 LSZH Fiber Patch Cable (LC/LC) - Aqua, 1M (3 ft.)

MODEL NUMBER: N820-01M



#### Highlights

- Designed for 10-Gig Ethernet applications...OM3 Rated
- Backward compatible with existing 50/125 fiber
- Max 10Gb distance of 300 meters @850nm
- Low-Smoke, Zero Halogen (LSZH) Aqua jacket

#### Package Includes

- 1 meter ( 3ft ) Duplex Multimode 50/125 Aqua OM3 Fiber Patch Cable, LC/LC

#### Features

- 1 Meter ( 3ft ) LC/LC, OM3 Rated
- 10gb Ethernet speed to 300 meters @850nm
- Use with VCSEL and LED laser light sources
- High-Speed, High-Bandwidth, Low-Cost
- Backward compatible with legacy LAN's
- Ideal for Fibre Channel (SAN) applications
- IEEE 802.3ae and TIA LOMMF compliant

## Specifications

| OVERVIEW             |                  |
|----------------------|------------------|
| UPC Code             | 037332134677     |
| Technology           | Multimode        |
| Optical Mode         | OM3              |
| CONNECTIONS          |                  |
| Side A - Connector 1 | LC DUPLEX (MALE) |
| Side B - Connector 1 | LC DUPLEX (MALE) |
| Endface Polish       | PC               |



Powering Business Worldwide

TRIPP LITE  
SERIES

| PHYSICAL                        |   |
|---------------------------------|---|
| Cable Jacket Color              | Aqua  |
| Connector Color                 | White   |
| Cable Jacket Material           | LSZH  |
| Cable Jacket Rating             | OFNR  |
| Clad Diameter (microns)         | 125   |
| Core Diameter (microns)         | 50  |
| Number of Fibers                | 2   |
| Cable Length (ft.)              | 3.3   |
| Cable Length (m)                | 1.01  |
| Cable Length (in.)              | 39.4  |
| Minimum Bend Radius             | 20 mm (Dynamic); 10 mm (Static)                       |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50                                    |
| Shipping Dimensions (hwd / cm)  | 22.86 x 17.78 x 1.27                                  |
| Shipping Weight (lbs.)          | 0.04  |
| Shipping Weight (kg)            | 0.02  |
| Fiber Cable Length              | 1M (3.3 ft)   |
| ENVIRONMENTAL                   |   |
| Operating Temperature Range     | -4° to 140°F (-20° to 60°C)                           |
| Storage Temperature Range       | -4° to 140°F (-20° to 60°C)                           |
| Operating Humidity Range        | 5% to 85% RH, Non-Condensing                          |
| Storage Humidity Range          | 35% to 65% RH, Non-Condensing                         |
| COMMUNICATIONS                  |   |
| Network Compatibility           | 1 Gbps (Gigabit); 10 Gbps; 25 Gbps; 40 Gbps; 100 Gbps |
| Attenuation @ 850NM             | 3.0 dB/km   |
| Insertion Loss                  | 0.20 dB   |
| FEATURES & SPECIFICATIONS       |   |
| Push/Pull Tabs                  | No  |
| Breakout                        | No  |
| Trunk                           | No  |
| STANDARDS & COMPLIANCE          |   |
| Product Compliance              | RoHS; REACH   |

WARRANTY & SUPPORT

|  |                           |
|--|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.