


## 40/100/400G Multimode 50/125 OM3 Fiber Optic Cable (12F MTP/MPO-PC to 4x Duplex LC/PC F/M), LSZH, Aqua, 2 m (6.6 ft.)

MODEL NUMBER: N844X-02M-8L-P



40/100/400 GbE Ethernet cable extends high-density network connections in enterprise applications in data centers, telecom rooms and wiring closets.

### Features

#### 40/100/400 GbE Cable Supports Higher Bandwidths Needed for High-Density Data Networking

The N844X-02M-8L-P is a premium multimode fiber optic cable that supports 400 Gb Ethernet speeds for transmitting data and voice signals over short distances. It is designed to support higher bandwidths for high-density patching between data center MDFs and IDF in enterprise installations. This multimode 50/125 OM3 cable is an ideal choice for 100 Gb Ethernet applications up to 100 meters (328 feet) at 850 nm. It is also backward compatible with 10 Gb and 25 Gb networks, so you can future-proof your current application for an eventual upgrade to 100 Gb or 400 Gb.

#### Switchable LC Connectors Allow Easy Polarity Conversions

The switchable LC/PC duplex ends let you easily switch the fiber polarity without tools or the need to re-terminate the connectors. This cable lets you extend the length of your connection and eliminates the need for longer fan-out cables or individual long duplex cable runs.

#### Aqua-Colored Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The OM3-rated cable has an aqua jacket to identify it as multimode in a crowded patch panel or switch and prevent it from becoming accidentally disconnected. The round low-smoke zero-halogen (LSZH) jacket limits the amount of toxic smoke emitted in case of combustion, making it suitable for poorly ventilated areas.

## Specifications

| OVERVIEW     |              |
|--------------|--------------|
| UPC Code     | 037332272928 |
| Technology   | Multimode    |
| Optical Mode | OM3          |

### Highlights

- OM3-rated cable recommended for 400 Gb speeds up to 100 meters (@ 850 nm)
- Switchable LC connectors allow polarity conversion without tools or re-termination
- Backward compatible with 10/25/40/100 Gb networks to facilitate future-proofing
- Aqua LSZH jacket allows fast, easy identification in a crowded switch or patch panel

### Package Includes

N844X-02M-8L-P 40/100/400G Multimode 50/125 OM3 Fiber Optic Cable, Aqua, 2 m (6.6 ft.)

|                                      |   |
|--------------------------------------|---|
| Mode Type                            | Multimode   |
| <b>PHYSICAL</b>                      |   |
| Cable Jacket Color                   | Aqua  |
| Connector Color                      | Beige; Black  |
| Cable Jacket Material                | LSZH  |
| Cable Jacket Rating                  | OFNR  |
| Cable Outer Diameter (OD)            | 3.0MM   |
| Clad Diameter (microns)              | 125.0   |
| Core Diameter (microns)              | 50.0  |
| Primary Coating Diameter (microns)   | 245.0   |
| Number of Fibers                     | 8   |
| Cable Length (ft.)                   | 6.56  |
| Cable Length (m)                     | 2.00  |
| Cable Length (in.)                   | 78.7  |
| Minimum Bend Radius                  | 20MM (DYNAMIC); 10MM (STATIC)   |
| <b>ENVIRONMENTAL</b>                 |   |
| Operating Temperature Range          | 14 TO 140 F (-10 TO 60 C)   |
| Storage Temperature Range            | 14 TO 140 F (-10 TO 60 C)   |
| Operating Humidity Range             | 5% TO 85% RH, NON-CONDENSING  |
| Storage Humidity Range               | 5% TO 85% RH, NON-CONDENSING  |
| <b>COMMUNICATIONS</b>                |   |
| Network Compatibility                | 40 Gbps; 100 Gbps; 400 Gbps   |
| Wavelength                           | 1300nm; 850nm   |
| Attenuation @ 850NM                  | 3.5dB/KM  |
| Attenuation @ 1300NM                 | 1.5dB/KM  |
| Insertion Loss                       | MTP/MPO: LESS THAN OR EQUAL TO 0.35dB; LC: LESS THAN OR EQUAL TO 0.20dB |
| <b>CONNECTIONS</b>                   |   |
| Side A - Connector 1                 | 12-STRAND MTP/MPO (FEMALE)  |
| Side B - Connector 1                 | (4) LC DUPLEX (MALE)  |
| Endface Polish                       | PC  |
| <b>FEATURES &amp; SPECIFICATIONS</b> |   |
| Push/Pull Tabs                       | No  |

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

|                                     |                           |
|-------------------------------------|---------------------------|
| Optical Port                        | LC; MPO/MTP               |
| Breakout                            | Yes                       |
| Trunk                               | Yes                       |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Certifications              | UL 1666                   |
| Product Compliance                  | RoHS; CE (Europe); REACH  |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

# TRIPP-LITE

by **EAT•N**

© 2022 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.