

## J-Hook Cable Support - 3/4", Batwing, Galvanized Steel, 25 Pack

MODEL NUMBER: NCM-JHC08-25



Galvanized batwing J-hooks help manage and organize category, fiber optic and other cables over long distances.

### Features

#### J-Hooks: An Inexpensive Alternative to Cable Trays

These 3/4-inch batwing J-hooks are recommended for setting up network or digital signage installations that require cabling to be run above drop ceilings, below raised floors or through inner duct systems for long distances. Tripp Lite's NCM-JHC08-25 comes with 25 swiveling batwing J-hooks that attach to a threaded rod or ceiling wire.

#### Designed to Accommodate a Wide Assortment of Cable Types

Less expensive and more flexible than cable trays or ladder rack runways, these J-hooks accommodate Cat5e/6/6a, fiber optic, audio/video, coaxial and other cable types. They comply with TIA-56B-C, TIA-569-C and ISO/IEC 14763-2 requirements for structured cabling systems, making them a perfect accessory for contractors, IT staff and cable installers.

#### Made from Galvanized Steel to Provide Proper Long-Term Support

These easy-to-install J-hooks are made from 18-gauge galvanized steel with a zinc-plated finish. To give you an idea of their strength, they offer stress-free support for up to 10 Cat5e cables, 15 Cat6 cables or five Cat6a cables. Maximum weight capacity is 60 pounds. Built-in anchor points allow you to use cable ties (sold separately) to secure cabling in place.

### Highlights

- Recommended for network and digital signage cabling above ceilings or below floors
- Made from galvanized steel designed to hold long lengths of cabling up to 60 lb.
- Offers stress-free support for wide range of cables, including fiber, A/V and Cat5e/6
- Built in anchor points allow use of cable ties to hold cables in place
- Package includes 25 batwing J-hooks that comply with TIA/EIA requirements

### Applications

- Neatly bundle cable above a drop ceiling or below a raised floor in your data center, network installation or digital signage setup

### Package Includes

- (25) 3/4" J-Hooks, Batwing, Galvanized Steel

## Specifications

OVERVIEW	
UPC Code	037332236050
PHYSICAL	
Color	Silver
Maximum Weight Capacity (kg)	27



Maximum Weight Capacity (lbs.)	60
Unit Dimensions (hwd / cm)	7.9 x 2.15 x 1.9
Unit Dimensions (hwd / in.)	3.11 x 0.86 x 0.75
Unit Weight (kg)	0.03
Unit Weight (lbs.)	0.073
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	N/A
Storage Temperature Range	N/A
Relative Humidity	N/A
<b>CERTIFICATIONS</b>	
Certifications	Tested to RoHS, REACH. Compliant with TIA-56B-C, TIA-569-C, ISO/IEC 14763-2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2019 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>