

## J-Hook Cable Support - 3/4", Wall Mount, Galvanized Steel, 25 Pack

MODEL NUMBER: NCM-JHW08-25



Galvanized wall-mount J-hooks help manage and organize category, fiber optic and other cables over long distances.

### Features

#### J-Hooks: An Inexpensive Alternative to Cable Trays

These 3/4-inch wall-mount J-hooks are recommended for setting up network or digital signage installations that require cabling to be run along walls, ceilings and raised floors for long distances. Tripp Lite's NCM-JHW08-25 comes with 25 wall-mount J-hooks.

#### Designed to Accommodate a Wide Assortment of Cable Types

Less expensive and more flexible than cable trays or ladder rack runways, these J-hooks accommodate Cat5e/6/6a, fiber optic, audio/video, coaxial and other cable types. They comply with TIA-56B-C, TIA-569-C and ISO/IEC 14763-2 requirements for structured cabling systems, making them a perfect accessory for contractors, IT staff and cable installers.

#### Made from Galvanized Steel to Provide Proper Long-Term Support

These easy-to-install J-hooks are made from 18-gauge galvanized steel with a zinc-plated finish. To give you an idea of their strength, they offer stress-free support for up to 10 Cat5e cables, 15 Cat6 cables or five Cat6a cables. Maximum weight capacity is 60 pounds. Built-in anchor points allow you to use cable ties (sold separately) to secure cabling in place.

## Specifications

OVERVIEW	
UPC Code	037332236081
Accessory Type	Cable Support
Accessory Class	Audio Video Accessories
PHYSICAL	

### Highlights

- Recommended for network and digital signage cabling along walls and ceilings
- Made from galvanized steel designed to hold long lengths of cabling up to 60 lb.
- Offers stress-free support for wide range of cables, including fiber, A/V and Cat5e/6
- Built-in anchor points allow use of cable ties to hold cables in place
- Package includes 25 wall-mount J-hooks that comply with TIA/EIA requirements

### Applications

- Neatly bundle cable along a wall, ceiling or raised floor in your data center, network installation or digital signage setup

### Package Includes

- (25) 3/4" J-Hooks, Wall Mount, Galvanized Steel

Color	Silver
Cable Jacket Color	Silver
Maximum Weight Capacity (lbs.)	60
Maximum Weight Capacity (kg)	27
Unit Dimensions (hwd / in.)	3.110 x 0.860 x 0.750
Unit Dimensions (hwd / cm)	7.9 x 2.15 x 1.9
Unit Weight (lbs.)	0.0556
Unit Weight (kg)	0.03
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	ISO/IEC 14763-2; RoHS; TIA-568-C; TIA-569-C; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty