

J-Hook Cable Support - 4", Wall Mount, Galvanized Steel, 25 Pack

MODEL NUMBER: NCM-JHW40-25



Galvanized wall-mount J-hooks help manage and organize category, fiber optic and other cables over long distances.

Features

J-Hooks: An Inexpensive Alternative to Cable Trays

These four-inch wall-mount J-hooks are recommended for setting up network or digital signage installations that require cabling to be run along walls, ceilings and raised floors for long distances. Tripp Lite's NCM-JHW40-25 comes with 25 wall-mount J-hooks.

Designed to Accommodate a Wide Assortment of Cable Types

Less expensive and more flexible than cable trays or ladder rack runways, these J-hooks accommodate Cat5e/6/6a, fiber optic, audio/video, coaxial and other cable types. They comply with TIA-56B-C, TIA-569-C and ISO/IEC 14763-2 requirements for structured cabling systems, making them a perfect accessory for contractors, IT staff and cable installers.

Made from Galvanized Steel to Provide Proper Long-Term Support

These easy-to-install J-hooks are made from 18-gauge galvanized steel with a zinc-plated finish. To give you an idea of their strength, they offer stress-free support for up to 330 Cat5e cables, 220 Cat6 cables or 80 Cat6a cables. Maximum weight capacity is 60 pounds. Built-in anchor points allow you to use cable ties (sold separately) to secure cabling in place.

Highlights

- Recommended for network and digital signage cabling along walls and ceilings
- Made from galvanized steel designed to hold long lengths of cabling up to 60 lb.
- Offers stress-free support for wide range of cables, including fiber, A/V and Cat5e/6
- Built-in anchor points allow use of cable ties to hold cables in place
- Package includes 25 wall-mount J-hooks that comply with TIA/EIA requirements

Applications

- Neatly bundle cable along a wall, ceiling or raised floor in your data center, network installation or digital signage setup

Package Includes

- (25) 4" J-Hooks, Wall Mount, Galvanized Steel

Specifications

OVERVIEW	
UPC Code	037332236111
Accessory Type	Cable Support
Accessory Class	Audio Video Accessories

PHYSICAL	
Color	Silver
Cable Jacket Color	Silver
Maximum Weight Capacity (lbs.)	60
Maximum Weight Capacity (kg)	27
Unit Dimensions (hwd / in.)	7.210 x 1.850 x 4.000
Unit Dimensions (hwd / cm)	18.02 x 4.7 x 10.16
Unit Weight (lbs.)	0.4555
Unit Weight (kg)	0.21
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	ISO/IEC 14763-2; RoHS; TIA-568-C; TIA-569-C; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty