

SmartRack 4-Post Rack-Mount Rail Kit for the Robotic Fiber Panel System

MODEL NUMBER: NRFP-BRKT



Rail kit required for mounting Tripp Lite's NRFP Robotic Fiber Panel System in your 4-post rack enclosure.

Features

For Mounting Your Tripp Lite NRFP Robotic Fiber Panel System The NRFP-BRKT comes with two pre-assembled slider rail units, each with loose screws to let you make manual adjustments. Each unit includes rear and front brackets, a stiffener, a slider and six socket-head cap screws. Also included with the kit are four positioning rulers (two each for WECO and EIA racks), a clearance/level tool to ensure proper clearance and leveling of the NRFP chassis, and a cantilever tray for rear support of the NRFP-LCU-1 (sold separately). The NRFP-BRKT is required for mounting the NRFP-500MM-CP in a 4-post rack-mount application.

Highlights

- Includes 2 pre-assembled slider rail units with loose screws for easy adjusting
- Each unit includes rear/front brackets, stiffener, slider and 6 socket-head cap screws
- Adjustable for mounting depths between 36 in. and 43 in. (914 mm–1092 mm)
- Also comes with positioning rulers, clearance/level tool and cantilever tray for LCU
- Required for rack-mounting the NRFP Robotic Fiber Panel System in a 4-post rack

Applications

- Mount a Tripp Lite NRFP Robotic Fiber Panel System in a 4-post rack enclosure

System Requirements

- Required for mounting the NRFP-500MM-CP in a 4-post rack-mount application

Package Includes

- (2) ROME slider rail units
- (4) ROME positioning rulers (2 WECO, 2 EIA)
- Clearance/level tool (jig)
- Cantilever tray for rear LCU support

Specifications

| OVERVIEW | |
|-----------------------------|------------------------|
| UPC Code | 037332236999 |
| Accessory Type | Rack-Mount Rail Kit |
| Accessory Class | Rack Accessories |
| PHYSICAL | |
| Color | Silver |
| Material of Construction | Steel |
| Unit Dimensions (hwd / in.) | 2.000 x 1.130 x 29.500 |
| Unit Weight (lbs.) | 44 |



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States

| | |
|--------------------------------------|-------------------------|
| Unit Weight (kg) | 19.96 |
| CONNECTIONS | |
| Crossover Wiring | No |
| FEATURES & SPECIFICATIONS | |
| Snagless Connector | No |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |



Powering Business Worldwide

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.