

P002-000 does not transform voltage. Verify your device or power supply is within the output range before use.

## NEMA 5-15R to C14 Power Cord Adapter - 10A, 125V, Black

MODEL NUMBER: P002-000



### Highlights

- Recommended for powering computers, printers and other peripherals
- Converts a NEMA 5-15P connector into a C14 connector to match available outlet

### Applications

- Connect devices like computers, printers and monitors to a C13 outlet near your workstation

### Package Includes

- P002-000 NEMA 5-15R to C14 Power Cord Adapter, Black

5-15R to C14 adapter allows you to connect your PC or other device with a NEMA 5-15P plug to a UPS with a C13 power outlet.

### Features

**C14 to NEMA 5-15R Adapter Connects Computers, Monitors and Other Equipment** This UL-listed power cord adapter is designed for low-voltage home/office setups. It converts a NEMA 5-15P plug into a C14 connector and is ideal for a device's built-in power cord that doesn't match the available outlet. You can use this adapter to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to an AC wall outlet or UPS system with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time.

## Specifications

| OVERVIEW                    |   |
|-----------------------------|---|
| UPC Code                    | 037332217936                                      |
| Device Compatibility        | Computer; Monitor/HDTV; Printer; UPS; PDU; Server |
| Country/Region              | North America                                     |
| INPUT                       |   |
| Maximum Input Amps          | 10  |
| Voltage Compatibility (VAC) | 125   |
| PHYSICAL                    |   |
| Color                       | Black   |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                           |
|-------------------------------------|---------------------------|
| Wire Gauge (OD - mm <sup>2</sup> )  | N/A                       |
| Power Cord Jacket Type              | N/A                       |
| Shipping Dimensions (hwd / cm)      | 12.70 x 10.11 x 1.27      |
| Shipping Dimensions (hwd / in.)     | 5.00 x 3.98 x 0.50        |
| Shipping Weight (kg)                | 0.05                      |
| Shipping Weight (lbs.)              | 0.11                      |
| <b>ENVIRONMENTAL</b>                |                           |
| Operating Temperature Range         | 14 to 140 F (-10 to 60 C) |
| Storage Temperature Range           | 14 to 140 F (-10 to 60 C) |
| Relative Humidity                   | 30-80% RH                 |
| <b>CONNECTIONS</b>                  |                           |
| Side A - Connector 1                | IEC-320-C14               |
| Side B - Connector 1                | NEMA 5-15R                |
| <b>SPECIAL FEATURES</b>             |                           |
| High Voltage                        | No                        |
| Locking Plug                        | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Certifications                      | UL/cUL, RoHS, REACH       |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>