

NEMA 5-15R to C14 Computer AC Power Cable - 10A, 125V, 18 AWG, 1 ft., Black

MODEL NUMBER: P002-001-10A



Computer AC power cable allows you to connect your PC or other device with a NEMA 5-15P plug to a PDU or UPS with a C13 power outlet.

Features

Computer AC Power Cable Connects Computers, Monitors and Other Equipment This computer AC power cable is designed for low-voltage data center, server room or home/office applications. This NEMA 5-15R to C14 cord converts a NEMA 5-15P plug into a C14 connector. You can use it to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a surge protector, UPS system or PDU with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time. The one-foot length helps reduce cable clutter.

Specifications

Highlights

- Recommended for powering computers, printers and other peripherals
- Adds 1 ft. to your existing power connection to provide flexibility in placing devices
- NEMA 5-15R to C14 extension cord is ideal replacement for worn-out or missing cable
- Can connect a C13 peripheral to a PC's switched source to save energy and free up an outlet on your surge protector or PDU

Applications

- Connect devices like computers, printers and monitors to a PDU up to 1 ft. away in your workstation
- Extend an existing power connection up to 1 ft. to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord
- Power your monitor through a switched source on your PC to free up an outlet on your surge protector or PDU

Package Includes

- P002-001-10A NEMA 5-15R to C14 Computer AC Power Cable, 1 ft., Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332180377
Country/Region	North America
INPUT	
Maximum Input Amps	10
Cable Length (ft.)	1
Cable Length (m)	0.3
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Weight (kg)	0.10
Shipping Weight (lbs.)	0.22
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	NEMA 5-15R
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>