

NEMA 5-15R to C14 Computer AC Power Cable - 13A, 125V, 16 AWG, 1 ft. (0.31 m), Black

MODEL NUMBER: P002-001-13A



Computer AC power cable allows you to connect your PC or other device with a NEMA 5-15P plug to a PDU or UPS with a C13 power outlet.

Features

Computer AC Power Cable Connects Computers, Monitors and Other Equipment

This computer AC power cable is designed for low-voltage data center, server room or home/office applications. The NEMA 5-15R to C14 cord converts a NEMA 5-15P plug into a C14 connector. You can use it to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a surge protector, UPS system or PDU with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time. The one-foot (0.3-meter) length helps reduce cable clutter.

Specifications

OVERVIEW	
UPC Code	037332290038
Device Compatibility	Computer; Monitor/HDTV; PDU; Printer; Server; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	13.0
Voltage Compatibility (VAC)	125
Cable Voltage Rating	125
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	NEMA 5-15R

Highlights

- Recommended for powering computers, printers and other peripherals
- Adds 1 ft. to your existing power connection to provide flexibility in placing devices
- NEMA 5-15R to C14 extension cord is ideal replacement for worn-out or missing cable
- Can connect a C13 peripheral to a PC's switched source to save energy and free up an outlet on your surge protector or PDU

Package Includes

P002-001-13A NEMA 5-15R to C14 Computer AC Power Cable, 1 ft. (0.3 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Connector Type	Molded
Connector Style	Straight
Latching or Gripping Connector	No
Angled Connector	No
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	SJT
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.5mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	8.5
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	10.98 x 7.00 x 0.50
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	10.980 x 7.000 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.154
Unit Weight (kg)	0.07
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Relative Humidity	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.