

NEMA 5-15R to C14 Computer AC Power Cable - 13A, 125V, 16 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P002-002



Computer AC power cable allows you to connect your PC or other device with a NEMA 5-15P plug to a PDU or UPS with a C13 power inlet.

Features

Computer AC Power Cable Connects Computers, Monitors and Other Equipment This computer AC power cable is designed for low-voltage data center, server room or home/office applications. It converts a NEMA 5-15P plug into a C14 connector. You can use it to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a surge protector, UPS system or PDU with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time. The 2-ft. (0.61 m) length helps reduce cable clutter.

Highlights

- Recommended for powering computers, printers and other peripherals
- Adds 2-ft. (0.61 m) to your existing power connection to provide flexibility in placing devices
- NEMA 5-15R to C14 extension cord is ideal replacement for worn-out or missing cable
- Can connect a C13 peripheral to a PC's switched source to save energy and free up an outlet on your surge protector or PDU

Applications

- Connect devices like computers, printers and monitors to a PDU up to 2-ft. (0.61 m) away in your workstation
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord
- Power your monitor through a switched source on your PC to free up an outlet on your surge protector or PDU

Package Includes

- P002-002 NEMA 5-15R to C14 Computer AC Power Cable, 2-ft. (0.61 m), Black

Specifications

OVERVIEW	
UPC Code	037332013361
Device Compatibility	Computer; Monitor/HDTV; Printer; UPS; PDU; Server
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125



PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.5mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	NEMA 5-15R
FEATURES & SPECIFICATIONS	
High Voltage	No
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Compliance	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>