

## NEMA 5-15R to C14 Computer AC Power Cable - 10A, 125V, 18 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P002-002-10A



Computer AC power cable allows you to connect your PC or other device with a NEMA 5-15P plug to a PDU or UPS with a C13 power outlet.

### Features

**Computer AC Power Cable Connects Computers, Monitors and Other Equipment** This computer AC power cable is designed for low-voltage data center, server room or home/office applications. This NEMA 5-15R to C14 cord converts a NEMA 5-15P plug into a C14 connector. You can use it to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a surge protector, UPS system or PDU with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time. The 2-ft. (0.61 m) length helps reduce cable clutter.

### Highlights

- Recommended for powering computers, printers and other peripherals
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacement for worn-out or missing NEMA 5-15R to C14 extension cord
- Can connect a C13 peripheral to a PC's switched source to save energy

### Applications

- Connect devices like computers, printers and monitors to a PDU up to 2-ft. (0.61 m) away in your workstation
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord
- Power your monitor through a switched source on your PC, thus freeing up an outlet on your surge protector or PDU

### Package Includes

- P002-002-10A NEMA 5-15R to C14 Computer AC Power Cable, 2-ft. (0.61 m), Black

## Specifications

OVERVIEW	
UPC Code	037332180384
Device Compatibility	Computer; Monitor/HDTV; Printer; UPS; PDU; Server
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	IEC-320-C14



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	NEMA 5-15R
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	10.00 x 7.70 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 19.56 x 0.25
Shipping Weight (lbs.)	0.26
Shipping Weight (kg)	0.12
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.