



NEMA 5-15R to C14 Computer AC Power Cable - 10A, 125V, 18 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P002-002-10A











Computer AC power cable allows you to connect your PC or other device with a NEMA 5-15P plug to a PDU or UPS with a C13 power outlet.

Features

Computer AC Power Cable Connects Computers, Monitors and Other EquipmentThis computer AC power cable is designed for low-voltage data center, server room or home/office applications. This NEMA 5-15R to C14 cord converts a NEMA 5-15P plug into a C14 connector. You can use it to connect a computer, monitor, printer or other device with a NEMA 5-15P plug to a surge protector, UPS system or PDU with C13 power outlets. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time. The 2-ft. (0.61 m) length helps reduce cable clutter.

Highlights

- Recommended for powering computers, printers and other peripherals
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacement for worn-out or missing NEMA 5-15R to C14 extension cord
- Can connect a C13 peripheral to a PC's switched source to save energy

Applications

- Connect devices like computers, printers and monitors to a PDU up to 2-ft. (0.61 m) away in your workstation
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord
- Power your monitor through a switched source on your PC, thus freeing up an outlet on your surge protector or PDU

Package Includes

 P002-002-10A NEMA 5-15R to C14 Computer AC Power Cable, 2-ft. (0.61 m), Black

Specifications

OVERVIEW		
UPC Code	037332180384	
Device Compatibility	Computer; Monitor/HDTV; Printer; UPS; PDU; Server	
Country/Region	North America	
INPUT		
Maximum Input Amps	10	
Voltage Compatibility (VAC)	125	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14	





Side B - Connector 1	NEMA 5-15R	
PHYSICAL		
Plug Color	Black	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	FT2	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	7.7mm	
Number of Conductors		
	3	
Wire Gauge (AWG)	18	
Wire Gauge (OD - mm²)	0.82	
Cable Length (ft.)	2	
Cable Length (m)	0.61	
Shipping Dimensions (hwd / in.)	10.00 x 7.70 x 0.10	
Shipping Dimensions (hwd / cm)	25.40 x 19.56 x 0.25	
Shipping Weight (lbs.)	0.26	
Shipping Weight (kg)	0.12	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Operating Humidity Range	20% to 80% RH	
Storage Humidity Range	20% to 80% RH	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No	
High Voltage	No	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		





Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.