

Power Cord Y Splitter, C14 to 2x NEMA 5-15R - 13A, 125V, 16 AWG, 18 in. (46 cm), Black

MODEL NUMBER: P002-18N-2R



Power cord splitter allows two devices with NEMA 5-15P plugs to share one AC power input cord and one C13 outlet.

Features

Y-Style Power Cord Splitter Connects 2 Devices with 5-15P Plugs to One AC Outlet

This extension cable splitter allows two devices with NEMA 5-15P plugs to share one AC input cord and one C13 power outlet. The AC power splitter features a C14 inlet for connecting to an AC power source and two 5-15R ends for connecting to devices' power cords. By connecting two devices to one power outlet, the splitter frees up space in a PDU or surge protector, reduces cable clutter and allows welcome flexibility in placing equipment with respect to the outlet.

16 AWG Cable Powers a Wide Variety of Essential Electronics

With the P002-18N-2R, a single C13 outlet can power two devices, such as computers, monitors, scanners, printers and other equipment in your low-voltage data center, server room or home/office application. You can also connect your C13 printer or monitor to a switched source on your PC, allowing you to turn both devices on and off at the same time to cut energy costs.

Highlights

- Connects 2 devices to one AC inlet to save space and reduce cable clutter
- Recommended for powering dual computers, monitors or other home/office devices
- Can connect a C13 peripheral to a PC's switched source to save energy costs
- Ideal replacement for a worn-out or missing power cord Y splitter
- C14 inlet links to AC power; 5-15R ends connect to devices' power cords

Package Includes

P002-18N-2R Power Cord Y Splitter, 18 in. (46 cm), Black

Specifications

OVERVIEW	
UPC Code	037332273154
Device Compatibility	Computer; PDU; Printer; Scanner; Server; UPS
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
CONNECTIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	IEC-320-C14
Side B - Connector 1	(2) NEMA 5-15R
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.3 mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Cable Length (in.)	18
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH, Non-Condensing
Storage Humidity Range	20% to 80% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.