

PDU Power Cord, C13 to C14 - 13A, 250V, 16 AWG, 4 ft. (1.22 m), Black

MODEL NUMBER: P004-004-13A



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 4 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 4-ft. (1.22 m). The 4-ft. (1.22 m) length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 4-ft. (1.22 m) to your existing power connection to provide flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, servers and monitors to a PDU up to 4-ft. (1.22 m) away in your data center
- Extend an existing power connection up to 4-ft. (1.22 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-004-13A C14 Male to C13 Female Power Cable, 4-ft. (1.22 m), Black

Specifications

OVERVIEW	
UPC Code	037332180452
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.5mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	4
Cable Length (m)	1.22
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 0.25
Shipping Weight (lbs.)	0.42
Shipping Weight (kg)	0.19
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.