

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 4 ft. (1.22 m), Blue

MODEL NUMBER: P004-004-BL



Blue computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 4 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 4-ft. (1.22 m). The 4-ft. (1.22 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This computer power extension cord features a blue SJT jacket and fully molded blue ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332173218
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
PHYSICAL	

Highlights

- Recommended for powering computers, printers and other essential peripherals
- 4-ft. (1.22 m) length allows flexibility in placing devices, while avoiding cable clutter
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Color-coded blue for fast, easy identification in a crowded rack or workstation

Applications

- Connect devices like computers, servers and monitors to a PDU up to 4-ft. (1.22 m) away in your data center
- Extend an existing power connection up to 4-ft. (1.22 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-004 C14 Male to C13 Female Power Cable, 4-ft. (1.22 m), Blue

Plug Color	Blue
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	4
Cable Length (m)	1.22
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Weight (lbs.)	0.42
Shipping Weight (kg)	0.19
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty