

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 4 ft. (1.22 m), Yellow

MODEL NUMBER: P004-004-YW



Yellow computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 4 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 4-ft. (1.22 m). The 4-ft. (1.22 m) length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This computer power extension cord features a yellow SJT jacket and fully molded yellow ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

| OVERVIEW | |
|-----------------------------|---|
| UPC Code | 037332168351 |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region | Global |
| INPUT | |
| Maximum Input Amps | 10 |
| Voltage Compatibility (VAC) | 100-250 |
| PHYSICAL | |

Highlights

- Recommended for powering computers, printers and other essential peripherals
- 4-ft. (1.22 m) length allows flexibility in placing devices, while avoiding cable clutter
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Color-coded yellow for fast, easy identification in a crowded rack or workstation

Applications

- Connect devices like computers, servers and monitors to a PDU up to 4-ft. (1.22 m) away in your data center
- Extend an existing power connection up to 4-ft. (1.22 m) to more easily place a device or reach a power source near your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P004-004 C14 Male to C13 Female Power Cable, 4-ft. (1.22 m), Yellow



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--------------------------------------|-----------------------------|
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Plug Color | Yellow |
| Power Cord Jacket Type | SJT |
| Cable Jacket Rating | FT2 |
| Cable Outer Diameter (OD) | 7.70mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 18 |
| Wire Gauge (OD - mm ²) | 0.82 |
| Cable Length (ft.) | 4 |
| Cable Length (m) | 1.22 |
| Shipping Dimensions (hwd / cm) | 25.40 x 18.03 x 1.27 |
| Shipping Dimensions (hwd / in.) | 10.00 x 7.10 x 0.50 |
| Shipping Weight (kg) | 0.19 |
| Shipping Weight (lbs.) | 0.42 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4 TO 140 F (- 20° TO 60°C) |
| Storage Temperature Range | -4 TO 140 F (- 20° TO 60°C) |
| Operating Humidity Range | 20-80% RH |
| Storage Humidity Range | 20-80% RH |
| CONNECTIONS | |
| Side A - Connector 1 | IEC-320-C14 |
| Side B - Connector 1 | IEC-320-C13 |
| FEATURES & SPECIFICATIONS | |
| High Voltage | Yes |
| Locking Plug | No |
| Angled Plug | No |
| STANDARDS & COMPLIANCE | |
| Certifications | UL/Cul, RoHS, REACH |
| Approvals | UL /CSA |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>