

## PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 6 ft., Green

MODEL NUMBER: P004-006-AGN



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 6 ft.

### Features

**C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to six feet. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.

**Color-Coded to Avoid Misidentification That Can Cause Costly Downtime** This computer power extension cord features a green SJT jacket and fully molded green ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

### Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 6 ft. to your existing connection to provide more flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable
- Color-coded green for fast, easy identification in a crowded rack or workstation

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 6 ft. away in your data center
- Extend an existing power connection up to 6 ft. to more easily place a device or reach a power source away from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P004-006-AGN C14 Male to C13 Female Power Cable, 6 ft., Green

## Specifications

OVERVIEW	
UPC Code	037332198907



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Country/Region	North America
<b>INPUT</b>	
Maximum Input Amps	10
Cable Length (ft.)	6
Cable Length (m)	1.8
Cable Length (in.)	72
Voltage Compatibility (VAC)	250
Cable Length (cm)	182.88
<b>PHYSICAL</b>	
Color	Green
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Weight (kg)	0.23
Shipping Weight (lbs.)	0.51
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:  
<https://www.tripplite.com/products/product-certification-agencies>