

## PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 15 ft., Black

MODEL NUMBER: P004-015



Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 15 ft.

### Features

**C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 15 feet. The 15-foot length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 15 ft. to your existing power connection to provide flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 15 ft. away in your data center
- Extend an existing power connection up to 15 ft. to more easily place a device or reach a power source far from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P004-015 C14 Male to C13 Female Power Cable, 15 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332180483
Country/Region	North America
INPUT	



Maximum Input Amps	10
Cable Length (ft.)	15
Cable Length (m)	4.6
Voltage Compatibility (VAC)	100-250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.27 x 12.95 x 20.32
Shipping Dimensions (hwd / in.)	0.50 x 5.10 x 8.00
Shipping Weight (kg)	0.45
Shipping Weight (lbs.)	1.00
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>