

## PDU Power Cord, C13 to C14 - 10A, 250V, H05VV-F, 5 m (16.4 ft.), Black

MODEL NUMBER: P004-05M-EU



Extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 5 m.

### Features

#### C13-to-C14 Power Cord Connects Computers, Printers, Servers and Other Equipment

This durable extension cord is designed for small data centers, office workstations and other lower-amp applications. The power cable can be used to power a computer, server or monitor or to attach a server or drive to a PDU. It can also extend an existing connection up to five meters (16.4 feet) to right-size your current application and allow some flexibility in placing connected equipment.

#### H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm<sup>2</sup> enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks and other IT applications in Europe.

## Specifications

OVERVIEW	
UPC Code	037332280978
Product Type	PDU Power Cord
Device Compatibility	PDU
Country/Region	Europe
INPUT	
Maximum Input Amps	10.0
Voltage Compatibility (VAC)	250
PHYSICAL	

### Highlights

- Connects a PC or server to a PDU or UPS system in a data rack or cabinet
- Adds 5 m to your existing power connection to provide flexibility in placing devices
- Fully VDE-compatible for European IT applications
- Ideal replacement for worn-out or missing power cable

### Package Includes

P004-05M-EU C13 to C14 Power Cord, 5 m (16.4 ft.), Black

Plug Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.75
Power Cord Color	Black
Cable Length (ft.)	16.4
Cable Length (m)	5.00
Cable Length (cm)	500
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.95
Shipping Weight (kg)	0.43
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.95
Unit Weight (kg)	0.43
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C13
Side B - Connector 1	IEC-320-C14
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Armored Cable	No
Angled Plug	No
High Voltage	Yes

Locking Plug	No
Coiled Power Cord	No
Locking	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty