

Power Cord Splitter, C14 to 4xC13 PDU Style - 10A, 250V, 18 AWG, 18-in. (45.72 cm), Black

MODEL NUMBER: P004-18N-4XC13



C14-to-C13 splitter allows 4 devices with C14 inlets to share one AC power input cord and one C13 outlet on a PDU or UPS system.

Features

C14-to-C13 X-Style Splitter Cord Connects 4 Devices with C14 Inlets to One C13 Outlet This IEC-320-C14 to IEC-320-C13 splitter allows four devices with C14 power inlets to share one AC input cord and one C13 outlet. This C14 male to C13 female cord features a C14 end for connecting to an AC power source on a PDU, surge protector or UPS system and four C13 ends for connecting to devices. By connecting four devices to one outlet, the power cord splitter frees up space in a PDU or surge protector and helps reduce cable clutter.

IEC Cable Powers a Wide Variety of Essential Electronics With this PC power splitter, a single C13 outlet can power four devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this IEC cable is compatible with Tripp Lite power and extension cords.

Specifications

OVERVIEW	
UPC Code	037332205261
Device Compatibility	Computer; Monitor/HDTV; Printer; Scanner; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
PHYSICAL	

Highlights

- Connects 4 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering multiple computers, monitors or other compatible peripherals
- C14 end connects to PDU or UPS power; C13 ends connect to devices' C14 inlets
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect 4 devices like computers, monitors, scanners and printers to one power outlet in your home office, work space or dorm room
- Cut cable clutter by powering up to 4 monitors in a multi-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging 4 rack devices into one outlet

Package Includes

- P004-18N-4XC13 C14 Male to C13 Female Splitter, PDU Style, 18 in., Black

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJTW
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Shipping Dimensions (hwd / in.)	0.60 x 8.50 x 12.50
Shipping Dimensions (hwd / cm)	1.52 x 21.59 x 31.75
Shipping Weight (lbs.)	0.54
Shipping Weight (kg)	0.24
ENVIRONMENTAL	
Operating Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Storage Temperature Range	-4 F TO 140 F (-20 C TO 60 C)
Operating Humidity Range	10 TO 65% RH
Storage Humidity Range	10 TO 65% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	(4) IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	Yes
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH

WARRANTY & SUPPORT

Product Warranty Period
(Worldwide)

Lifetime limited warranty