

# Power Cord Splitter, C14 to 4xC13 PDU Style - 10A, 250V, 18 AWG, 18-in. (45.72 cm), Black

MODEL NUMBER: P004-18N-4XC13



C14-to-C13 splitter allows 4 devices with C14 inlets to share one AC power input cord and one C13 outlet on a PDU or UPS system.

## Features

**C14-to-C13 X-Style Splitter Cord Connects 4 Devices with C14 Inlets to One C13 Outlet** This IEC-320-C14 to IEC-320-C13 splitter allows four devices with C14 power inlets to share one AC input cord and one C13 outlet. This C14 male to C13 female cord features a C14 end for connecting to an AC power source on a PDU, surge protector or UPS system and four C13 ends for connecting to devices. By connecting four devices to one outlet, the power cord splitter frees up space in a PDU or surge protector and helps reduce cable clutter.

**IEC Cable Powers a Wide Variety of Essential Electronics** With this PC power splitter, a single C13 outlet can power four devices, such as computers, monitors, printers, instrument amplifiers and other equipment compatible with a C13 connector. Ideal for areas where AC outlets are limited, such as rack cabinets, this IEC cable is compatible with power and extension cords.

## Specifications

OVERVIEW	
UPC Code	037332205261
Device Compatibility	Computer; Monitor/HDTV; Printer; Scanner; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14

## Highlights

- Connects 4 devices to one AC outlet to save space and reduce cable clutter
- Recommended for powering multiple computers, monitors or other compatible peripherals
- C14 end connects to PDU or UPS power; C13 ends connect to devices' C14 inlets
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

## Applications

- Connect 4 devices like computers, monitors, scanners and printers to one power outlet in your home office, work space or dorm room
- Cut cable clutter by powering up to 4 monitors in a multi-monitor display mount with a single cord
- Save space in a 0U vertical rack-mount PDU by plugging 4 rack devices into one outlet

## Package Includes

- P004-18N-4XC13 C14 Male to C13 Female Splitter, PDU Style, 18 in., Black



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	(4) IEC-320-C13
<b>PHYSICAL</b>	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJTW
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm <sup>2</sup> )	0.82
Cable Length (ft.)	1.5
Cable Length (m)	0.46
Shipping Dimensions (hwd / in.)	0.60 x 8.50 x 12.50
Shipping Dimensions (hwd / cm)	1.52 x 21.59 x 31.75
Shipping Weight (lbs.)	0.54
Shipping Weight (kg)	0.24
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.