

Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 3 ft. (0.91 m), Orange

MODEL NUMBER: P005-003-AOR



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 3 ft.

Features

C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This computer power extension cord features an orange SJT jacket and fully molded orange ends. The color-coding allows easy, fast identification in a crowded rack or workstation and helps prevent the cable from becoming inadvertently disconnected.

Specifications

OVERVIEW	
UPC Code	037332198990
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14

Highlights

- Recommended for powering computers, servers and other network devices
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Color-coded orange for fast, easy identification in a crowded rack or workstation
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 3 ft. away in your data center
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P005-003-AOR Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 3 ft., Orange



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C13
PHYSICAL	
Plug Color	Orange
Cable Jacket Color	Orange
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (cm)	91.44
Shipping Dimensions (hwd / in.)	9.90 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	25.15 x 17.78 x 1.27
Shipping Weight (lbs.)	0.44
Shipping Weight (kg)	0.20
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.