

Heavy-Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P005-006



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 6 ft.

Features

C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, servers and other network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like computers, servers and monitors to a PDU up to 6-ft. (1.83 m) away in your data center
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P005-006 Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 6-ft. (1.83 m), Black

Specifications

OVERVIEW	
UPC Code	037332150004
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; Router; Network Switch; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.3mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	1.00 x 7.00 x 11.00
Shipping Dimensions (hwd / cm)	2.54 x 17.78 x 27.94
Shipping Weight (lbs.)	0.78
Shipping Weight (kg)	0.35
Unit Dimensions (hwd / in.)	1.000 x 7.000 x 11.000
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	WEEE
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.