

## Heavy Duty PDU Power Cord, C13 to Right Angle C14 - 15A, 250V, 14 AWG, 6 ft., Black

MODEL NUMBER: P005-006-14RA



Computer power extension cord with right-angle C14 plug allows connection of a PC, printer or monitor in tight spaces or awkward angles.

### Features

**C14-to-C13 Power Cable for Network Devices That Require a Heavy-Gauge Connection** This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.

**Right-Angle C14 Plug Makes Connecting in Tight Spaces Easier** The C13 to C14 right-angle cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C14 plug guides the computer power supply cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

### Highlights

- Right-angle C14 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering computers, servers and other network devices
- 6 ft. length allows flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 6 ft. away in your data center
- Extend an existing power connection up to 6 ft. to more easily place a device or reach a power source away from your workstation
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

### Package Includes

- P005-006-14RA C13 to Right-Angle C14 Power Cable, 6 ft., Black



## Specifications

| OVERVIEW                           |                              |
|------------------------------------|------------------------------|
| UPC Code                           | 037332179937                 |
| Country/Region                     | North America                |
| INPUT                              |                              |
| Maximum Input Amps                 | 15                           |
| Cable Length (ft.)                 | 6                            |
| Cable Length (m)                   | 1.8                          |
| Voltage Compatibility (VAC)        | 100-250                      |
| PHYSICAL                           |                              |
| Color                              | Black                        |
| Number of Conductors               | 3                            |
| Power Cord Jacket Type             | SJT                          |
| Shipping Dimensions (hwd / cm)     | 25.40 x 17.78 x 0.25         |
| Shipping Dimensions (hwd / in.)    | 10.00 x 7.00 x 0.10          |
| Shipping Weight (kg)               | 0.30                         |
| Shipping Weight (lbs.)             | 0.66                         |
| Wire Gauge (AWG)                   | 14                           |
| Wire Gauge (OD - mm <sup>2</sup> ) | 2.08                         |
| ENVIRONMENTAL                      |                              |
| Operating Temperature Range        | -4 F (-20 C) to 140 F (60 C) |
| Storage Temperature Range          | -4 F (-20 C) to 140 F (60 C) |
| Operating Humidity Range           | 10-85% RH                    |
| Storage Humidity Range             | 10-85% RH                    |
| CONNECTIONS                        |                              |
| Side A - Connector 1               | IEC-320-C14 - RIGHT ANGLE    |
| Side B - Connector 1               | IEC-320-C13                  |
| SPECIAL FEATURES                   |                              |
| High Voltage                       | Yes                          |
| Locking Plug                       | No                           |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| WARRANTY                            |                           |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>