

Heavy-Duty PDU Power Cable, C13 to C14 - 15A, 250V, 14 AWG, Green, 6 ft.

MODEL NUMBER: P005-006-GN



Computer power cord extends your existing C13-to-C14 power connection as much as 6 feet.

Features

Power Cable for Network Devices That Require a Heavy-Gauge Connection This 14 AWG C14-to-C13 computer power cord is appropriate for high power connections and a dependable solution for server applications that demand a higher-rated, heavier-gauge cable. You can use this computer power cable for connecting a server, hard drive, monitor or computer to a PDU or UPS system. It's a worthy upgrade or replacement for the power cable that came included with your device. At six feet, the P005-006-GN gives you some flexibility in placing your connected devices.

Green Connectors for Fast, Easy ID That Can Save Costly Downtime This six-foot computer power cable features fully molded green C14 and C13 connectors. This allows you to color-code your connection in a crowded workstation or rack, helping you quickly identify it and prevent an accidental disconnection.

Highlights

- Ideal for powering your server, computer or other network component
- PDU power cable upgrades or replaces the manufacturer's standard computer power cord
- 14 AWG construction designed to handle high power levels needed for powering large equipment
- Green connectors allow quick identification in a crowded workstation or rack
- 6 ft. power cable gives you flexibility in placing your devices away from an outlet

Applications

- Connect a computer, server, hard drive or display to a PDU or UPS up to 6 ft. away
- Replace or update the standard power cable provided by your device's original manufacturer
- Extend an existing power connection up to 6 ft. to more easily place a device or reach a power source in a rack

Package Includes

- P005-006-GN Heavy-Duty Power Cable, Green, 6 ft.

Specifications

OVERVIEW	
UPC Code	037332168368



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Country/Region	North America
INPUT	
Maximum Input Amps	15
Cable Length (ft.)	6
Cable Length (m)	1.8
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Color	Black; Green
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	25.40 x 18.03 x 1.27
Shipping Dimensions (hwd / in.)	10.00 x 7.10 x 0.50
Shipping Weight (kg)	0.32
Shipping Weight (lbs.)	0.71
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
ENVIRONMENTAL	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
SPECIAL FEATURES	
High Voltage	Yes
Locking Plug	No
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>