

## Heavy Duty PDU Power Cord, C13 to C14 - 15A, 250V, 14 AWG, 10 ft., Black

MODEL NUMBER: P005-010



Computer power extension cord connects devices with C13/C14 power connectors or extends your existing power connection by 10 ft.

### Features

**C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment** This IEC-320-C14 to IEC-320-C13 cable features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. This C14 male to C13 female cord can be used to connect a computer, server, monitor or drive to a UPS system or PDU or replace or upgrade the standard power cord provided by the device's manufacturer. The 10-foot length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- Recommended for powering computers, servers and other network devices
- 10 ft. length allows great flexibility in placing devices in relationship to AC outlet
- PDU-style cord replaces or upgrades standard power cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU up to 10 ft. away in your data center
- Extend an existing power connection up to 10 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P005-010 Heavy-Duty C13 to C14 PDU-Style Power Extension Cable, 10 ft., Black

## Specifications

OVERVIEW	
UPC Code	037332140906
Country/Region	North America



<b>INPUT</b>	
Maximum Input Amps	15
Cable Length (ft.)	10
Cable Length (m)	3.1
Voltage Compatibility (VAC)	100-250
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Weight (kg)	0.48
Shipping Weight (lbs.)	1.05
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	Yes
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>