

## PDU Power Cords, C13 to P-Lock C14 - Heavy-Duty, 15A, 250V, 14 AWG, 6 ft. (1.8 m), Black, 6 Pack

MODEL NUMBER: P005-E06-6



Connect computers, servers or switches to a PDU with a P-Lock C13 or C39 power connector and extend existing power connections by 6 ft.

### Features

#### C13-to-C14 Power Cables for Network Devices That Require a Heavy-Gauge Connection

These power extension cords feature 14 AWG wire suitable for high power connections, making them a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. The P005-E06-6 can be used to power computers, servers, switches or other devices commonly found in a small data center, office workstation or other lower-amp application. The six-foot (1.8-meter) length helps reduce cable clutter by providing a tailor-made fit between the device and the PDU in a crowded rack enclosure. Six PDU power cables are included, an ideal pack for large-scale equipment rollouts.

#### Forms a Special Locking Connection with a P-Lock Outlet

The P-Lock C14 connector forms a secure connection with a PDU with a P-Lock outlet, including Eaton G4 and newer PDUs with C13 and C39 outlets. The P-Lock connection helps reduce costly downtime caused by accidental cable disconnections in a crowded rack or PDU space. The P005-E06-6 lets you replace a non-locking C14/C13 cable or upgrade an entire PDU application by pairing with an Eaton PDU or other PDU with P-Lock outlets.

### Highlights

- Recommended for powering computers, servers and other network devices
- P-Lock C14 connector eliminates accidental cable disconnections in a crowded PDU
- Thick 14 AWG wire gauge manages high power levels required for larger equipment
- 6 ft. length allows flexibility in mounting devices within a rack while avoiding cable clutter
- 6 black PDU power cables included, ideal for large-scale equipment rollouts

### Package Includes

(6) PDU Power Cords, C13 to P-Lock C14, 6 ft. (1.8 m), Black

## Specifications

| OVERVIEW             |   |
|----------------------|---|
| UPC Code             | 037332292902                                      |
| Product Type         | PDU Power Cord                                    |
| Device Compatibility | Computer; Monitor/HDTV; Printer; Server; UPS; PDU |
| Country/Region       | North America                                     |
| INPUT                |   |
| Maximum Input Amps   | 15  |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                              |
|--------------------------------------|------------------------------|
| Voltage Compatibility (VAC)          | 100-250                      |
| <b>CONNECTIONS</b>                   |                              |
| Side A - Connector 1                 | IEC-320-C14                  |
| Side B - Connector 1                 | IEC-320-C13                  |
| <b>PHYSICAL</b>                      |                              |
| Plug Color                           | Black                        |
| Cable Jacket Color                   | Black                        |
| Connector Color                      | Black                        |
| Cable Jacket Material                | PVC                          |
| Cable Jacket Rating                  | VW-1                         |
| Power Cord Jacket Type               | SJT                          |
| Cable Outer Diameter (OD)            | 9.3mm                        |
| Number of Conductors                 | 3                            |
| Wire Gauge (AWG)                     | 14                           |
| Wire Gauge (OD - mm <sup>2</sup> )   | 2.08                         |
| Cable Length (ft.)                   | 6                            |
| Cable Length (m)                     | 1.83                         |
| Shipping Dimensions (hwd / in.)      | 18.11 x 14.17 x 0.50         |
| Shipping Weight (lbs.)               | 4.42                         |
| Shipping Weight (kg)                 | 2.00                         |
| Unit Dimensions (hwd / in.)          | 10.000 x 7.990 x 0.500       |
| <b>ENVIRONMENTAL</b>                 |                              |
| Operating Temperature Range          | 23° to 158°F (-5° to 70°C)   |
| Storage Temperature Range            | 14° to 140°F (-10° to 60°C)  |
| Relative Humidity                    | 35 TO 85% RH, Non-Condensing |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                              |
| Antibacterial                        | No                           |
| Angled Plug                          | No                           |
| High Voltage                         | Yes                          |
| Locking Plug                         | Yes                          |
| Coiled Power Cord                    | No                           |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                              |
| Product Certifications               | cUL Listed; UL Listed        |



Powering Business Worldwide

TRIPP LITE  
SERIES

**WARRANTY & SUPPORT**

Product Warranty Period  
(Worldwide)

Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.