

Computer Power Cord Adapter, NEMA 5-15P to Down Angle C13 - 10A, 125V, Black

MODEL NUMBER: P006-000-DA



5-15P to C13 adapter allows you to connect your PC, printer or monitor into a surge protector or UPS with a NEMA 5-15R outlet.

Features

5-15P to C13 Adapter Connects PCs, Printers, Monitors and Other Equipment This UL-listed angled power adapter is designed for home/office desktop computer setups. It converts a C14 plug into a NEMA 5-15P connector and is ideal for a device's built-in power cord that doesn't match the available outlet. You can use this adapter to connect a computer, monitor, printer, scanner or other device with a C14 connector to a NEMA 5-15R wall outlet, surge protector or UPS system. The C13 end is designed at an angle, which allows you to use it in tight spaces, such as flush against a wall or behind furniture.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- Converts a C14 connector into a NEMA 5-15P connector to match available outlet
- Down-angled form factor is ideal for tight spaces, such as flush against a wall

Applications

- Connect devices like computers, printers and monitors to a NEMA 5-15R outlet near your workstation
- Plug into a device placed in a hard-to-reach space, such as against a wall or behind a desk

Package Includes

- P006-000-DA NEMA 5-15P to Down-Angled C13 Power Cord Adapter, Black

Specifications

OVERVIEW	
UPC Code	037332217998
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	
Color	Black
Power Cord Jacket Type	N/A



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Dimensions (hwd / cm)	12.70 x 10.11 x 1.27
Shipping Dimensions (hwd / in.)	5.00 x 3.98 x 0.50
Shipping Weight (kg)	0.05
Shipping Weight (lbs.)	0.11
Wire Gauge (OD - mm ²)	N/A
ENVIRONMENTAL	
Operating Temperature Range	14 to 140 F (-10 to 60 C)
Storage Temperature Range	14 to 140 F (-10 to 60 C)
Operating Humidity Range	30-80% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13 - DOWN ANGLE
SPECIAL FEATURES	
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/cUL, RoHS, REACH
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>