

## Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 13A, 125V, 16 AWG, 2 ft. (0.61 m), Black

MODEL NUMBER: P006-002-13A



Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

### Features

**Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment** This computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

### Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 2-ft. (0.61 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacement for a worn-out or missing NEMA 5-15P to C13 extension cord

### Applications

- Connect devices like computers, printers and monitors to a PDU up to 2-ft. (0.61 m) away in your workstation
- Extend an existing power connection up to 2-ft. (0.61 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P006-002-13A NEMA 5-15P to C13 Desktop Computer AC Power Cable, 2-ft. (0.61 m), Black

## Specifications

OVERVIEW	
UPC Code	037332180537
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Maximum Input Amps	13
Cable Length (ft.)	2
Cable Length (m)	0.6
Voltage Compatibility (VAC)	125
<b>PHYSICAL</b>	
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.31
Color	Black
Number of Conductors	3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	1.27 x 1.27 x 15.75
Shipping Dimensions (hwd / in.)	0.50 x 0.50 x 6.20
Shipping Weight (kg)	0.14
Shipping Weight (lbs.)	0.30
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C13
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	No
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>