

Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 10A, 125V, 18 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P006-003-HG10



Connects your PC, mobile cart or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

Features

Hospital-Grade Power Cable is a Safe Solution for Medical Facilities This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The three-foot length allows you flexibility in placing equipment with respect to the power outlet.

Designed and Tested to Strict Hospital-Grade Standards This hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Specifications

OVERVIEW	
UPC Code	037332193230
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
PHYSICAL	

Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Medical power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 3 ft. away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P006-003-HG10 Hospital-Grade Power Cord, NEMA 5-15P to C13, 3 ft., Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Weight (kg)	0.15
Shipping Weight (lbs.)	0.32
ENVIRONMENTAL	
Operating Temperature Range	-4 TO 221 F (- 20° TO 105°C)
Storage Temperature Range	-4 TO 221 F (- 20° TO 105°C)
Operating Humidity Range	20-80% RH
Storage Humidity Range	20-80% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
High Voltage	No
Locking Plug	No
Angled Plug	No
STANDARDS & COMPLIANCE	
Certifications	UL/Cul
Approvals	UL /CSA
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>