

Computer AC Power Cable, NEMA 5-15P to C13 - 360-Degree Rotating Right-Angle 5-15P Plug, 10A, 125V, 18 AWG, 6 ft. (1.8 m), Black

MODEL NUMBER: P006-006-15RR



Connects your PC, printer or monitor to a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other Equipment

This computer power cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU with a NEMA 5-15R outlet. The six-foot (1.8-meter) length allows you flexibility in placing equipment away from the power outlet.

Rotating Flat Plug Allows an Easier Connection in Tight Spaces

The NEMA 5-15P input rotates 360 degrees, allowing you to connect it at any angle and making it easy to plug into a crowded wall outlet or surge protector without blocking adjacent outlets. The right-angle plug runs parallel to the outlet, so it can connect in a confined or hard-to-reach location, such as behind furniture, that leaves little space for cable bend.

Specifications

OVERVIEW	
UPC Code	037332298294
Device Compatibility	Computer; Laptop
Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	

Highlights

- Right-angle plug rotates 360° for easy connection in a confined location or crowded surge protector
- Recommended for powering computers, printers and other home/office peripherals
- 6 ft. length allows you extra flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing NEMA 5-15P to C13 power cable

Package Includes

P006-006-15RR NEMA 5-15P to C13 Computer Power Cable, 6 ft. (1.8 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	NEMA 5-15P - RIGHT ANGLE
Side B - Connector 1	IEC-320-C13
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	SJT
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	1.02
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	11.54 x 4.02 x 0.50
Shipping Dimensions (hwd / cm)	29.31 x 10.21 x 1.27
Shipping Weight (lbs.)	0.47
Shipping Weight (kg)	0.21
Unit Dimensions (hwd / in.)	11.540 x 4.020 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	23° to 158°F (-5° to 70°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	35% to 85% RH
Storage Humidity Range	35% to 85% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	Yes
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
P-Lock Power Cord	No
Locking Power Cord	No
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Certifications	CSA (Canada); UL Listed; cUL Listed
Product Compliance	WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.