

## Piggyback Extension Cord, NEMA 5-15P/5-15R to C13 - 13A, 125V, 16 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P006-006-515MF



Piggyback power cord allows two devices, such as a PC and monitor, to share one NEMA 5-15R outlet, freeing up valuable PDU space.

### Features

**Piggyback Extension Cord Connects 2 Devices to One AC Outlet** This piggyback extension cord allows two devices, such as computers, monitors, printers, instrument amplifiers and other equipment with C14 inlets, to connect to a single NEMA 5-15R outlet. It features a C13 end for connecting to one device and a combination 5-15P/5-15R end that allows a second 5-15P cord to be connected, doubling your electrical outlet capacity. By connecting two devices to one outlet, the 6-ft. (1.83 m) cable frees up space in a PDU or surge protector and allows some flexibility in placing equipment with respect to the power outlet.

## Specifications

OVERVIEW	
UPC Code	037332167781
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black

### Highlights

- Combination 5-15P/5-15R connector allows a second 5-15P cord to plug into it
- Recommended for powering dual computers, monitors or other compatible peripherals
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing piggyback extension cord

### Applications

- Connect 2 devices like computers, monitors, scanners and printers to one power outlet up to 6-ft. (1.83 m) away in your home office, work space or dorm room
- Save space in a 0U vertical rack-mount PDU by plugging two rack devices into one outlet

### Package Includes

- P006-006-515MF Piggyback Extension Cord, 6-ft. (1.83 m), Black

Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.31
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	0.50 x 4.00 x 4.70
Shipping Dimensions (hwd / cm)	1.27 x 10.16 x 11.94
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Storage Temperature Range	-4 TO 140 F (- 20° TO 60°C)
Operating Humidity Range	20-80% RH
Storage Humidity Range	20-80% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA 5-15P
Side A - Connector 2	NEMA 5-15R
Side B - Connector 1	IEC-320-C13
<b>FEATURES &amp; SPECIFICATIONS</b>	
High Voltage	No
Locking Plug	No
Antibacterial	No
Angled Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.